



**Instruction & Specification Manual for Permanent Fall Arrest Anchors:
#PPA-0001-003 for Installing the Rescue MUTT
-Addendum-**

Purpose:

This addendum is for the installation of UST #PPA-0001-003 anchorage point into wood poles for rescue, multi-use, and permanent fall arrest anchor point. The Rescue MUTT installs quickly with factory supplied ½” x 5” Kortik Pound-In Lag Screw Bolts. Simply pound in the two lag screws into the mounting holes on the anchor mounting plate into the wood pole making sure that the backing plate is flush against the pole so as to mate against the wood completely. The Kortik Pilot Point Drive Screws provide a simple and easy starting and driving feature. Tap the hammer and the pilot point is on target in the wood. A few well directed blows from the linemens hammer and the Drive Screw is in place. The screws are fabricated with standard square heads, rolled “fetter drive” threads and are hot dip galvanized. This addendum is to be used in conjunction with the UST Instruction & Specification Manual for #PPA-0001-001 available from www.utilityanchor.com or by calling us at (425) 577-3190.

Installation:

Step #1



Place MUTT at desired location

Step #2



Start the ½” x 5” Kortik Lag Screw bolts using a hammer

Step #3



Use 2 factory supplied fasteners supplied with the Rescue MUTT

Step #4



Make sure that both lag Screw Bolts are in all the way

Anchor Specifications:

Anchor Plate Material: 11 gauge hot-rolled steel hot-dipped galvanized or zinc coated. Rated for 5,000 pounds fall arrest
 Anchor D-Ring: Drop forged, proof loaded, hot dipped galvanized or zinc coated. Rated for 5,000 pounds/22.4 kn
 Anchor Coating: Hot-Dipped Galvanized or zinc coated
 Warning Label: Heavy-Duty 18oz. vinyl

Kortick Lag Bolt Specifications:

Bolt Diameter: ½” x 5”
 Bolt Coating: Hot-Dipped Galvanized
 Bolt Head: Standard Square Head
 Embedment Depth: Min. 5”
 Mfg. Part Number: K1684

*Utility Safety Technologies, Inc.
1521 South San Luis, Green Valley AZ 85614
(425) 577-3190*